

Vibrax

Vibrator

The wide-ranging vibration spectrum optimally processes any material. The functionally sophisticated handling enables comfortable use even under difficult conditions.

Advantages

- Bubble-free flow behavior using two wave ranges with 4 levels of intensity.
- Low transfer of the vibrations to the workbench as the housing is oscillation decoupled.
- Long service life using maintenance-free vibration magnet.

Details

- Uncomplicated adaptation of the intensity via the large lever switch using only one finger.
- Extremely quiet, ensuring a comfortable working atmosphere.
- Time-saving due to quickly cleaned elements.
- Non-tip and extremely stable even when high pressure is applied to the edges.
- No springing of the impression tray thanks to the soft tray rest.

Optional accessory

Vibrating sphere ensures uniform flow behavior during investing and pouring of impression trays.



tool included



easy use



silent



Always at the right frequency: ideal flow properties for all plaster and investment materials

Technical data

Permissible mains voltage	230 V 120 V 100 V 220 V
Permissible mains frequency	50 Hz 60 Hz
Power consumption	185 VA (230 V) 170 VA (120 V) 190 VA (100 V) 170 VA (220 V)
Mains input fuse	2 x 1.6 A(T)
Frequency	100 Hz (50 Hz)
Dimensions (W x H x D)	275 x 140 x 220 mm // 10.8 x 5.5 x 8.7"
Weight	~6,4 kg // ~14.1 lbs

Ordering information

Vibrax, 230 V	No. 18300000
Vibrax, 120 V	No. 18301000
Vibrax, 100 V	No. 18302000
Vibrax, 100 V	No. 18303000
Vibrax, 220 V	No. 18304000
Vibrating sphere, 1 piece	No. 18300001



Importers & Dealers in Quality Dental Goods

1102 Embassy Chambers, 3rd Road, Khar West, Mumbai - 400052, India
+91 22 6127 7777 +919930006127 sales@nkpatelandsons.com
www.nkpatelandsons.com @nkpatelandsons /nkpatelandsons